

Buyers guide

Screws

Shoulder screws

Set screws



	HSS	SHS	SHSS	HC	NTM
Part number	HSS	SHS	SHSS	HC	NTM
Diagram					
Standard	ISO 7379	-	-	DIN 916	DIN 975
Characteristics	centering or guidance by precision shoulder	centering or guidance by precision shoulder	centering or guidance by precision shoulder	force concentrated into cup lips	strong grip, won't damage the shaft
Material	hardened steel	stainless steel 303	S/steel 416 pretreated	stainless steel A2	stainless steel A2
Corrosion resistance	☆	☆☆☆	☆☆	☆☆☆	☆☆☆
Mechanical resistance	☆☆☆	☆☆	☆☆☆	☆☆	☆☆
Price	€	€€	€€€	€€	€€€
Pages	① 412 - 413	① 414 - 415	① 416 - 417	① 434 - 435	① 429















Nuts



	SHN	SHN-A	NIN	NINA	WING
Part number	SHN	SHN-A	NIN	NINA	WING
Description	hexagonal	hexagonal	hexagonal	hexagonal	butterfly
Standard	DIN 934	DIN 934	DIN 935	DIN 935	DIN 314/35
Characteristics	standard	standard	loosening anti-vibration	loosening anti-vibration	manually operated
Material	stainless steel A2	steel	stainless steel A2	steel	steel/S/steel A2
Corrosion resistance	☆☆☆	☆☆	☆☆☆	☆	☆/☆☆☆
Mechanical resistance	☆☆	☆☆	☆☆	☆☆	☆☆
Price	€	€	€€	€	€
Pages	① 438	① 438	① 439	① 439	① 440

Set screws

Assembly screws

						
NTMBR	NTMDL	CHC	CHC/SS	FHC	BHC	VTH
						
-	-	DIN 912	DIN 912	DIN 7991	ISO 7380	DIN 933
strong grip won't damage the shaft	strong grip, won't damage the shaft	head can be countersunk	head can be countersunk	centering, head can be countersunk	round head	strong tightening
steel	steel	steel	stainless steel A2	stainless steel A2	stainless steel A2	steel
☆	☆	☆	☆☆☆	☆☆☆	☆☆☆	☆
☆☆	☆☆	☆☆☆	☆☆	☆☆	☆☆	☆☆
€	€	€	€€	€€	€€	€€
1 432 - 433	1 430 - 431	1 420 - 423	1 424 - 425	1 426 - 427	1 428	1 418 - 419

Washers



Part number	SHW	SHWA	RCX, RCC
Description	simple	simple	concave or convex
Standard	DIN 125	DIN 125	-
Characteristics	standard	standard	ensures good seating of screw-head
Material	stainless steel A2	steel	stainless steel
Corrosion resistance	☆☆☆	☆	☆☆☆
Mechanical resistance	☆☆	☆☆	☆☆
Price	€	€	€€
Pages	1 437	1 437	1 436