



Custom-made gears

STANDARD PARTS ADAPTED TO YOUR NEEDS

Modifications		Steel	Plastic
Bore-size (mm) free for 20 or more	< $\phi 25$	7,65 €	1,75 €
	$\phi 25$ to $\phi 50$	13,80 €	3,20 €
	$\geq \phi 50$	44,15 €	9,85 €
Key (mm)	< 8	6,10 €	1,65 €
	8 to 18	11,20 €	4,60 €
	≥ 20	20,10 €	8,65 €
Threaded hole	< M8	3,80 €	1,20 €
	$\geq M8$	4,80 €	2,00 €
Pinhole (mm)	< $\phi 8$	2,00 €	0,82 €
	$\geq \phi 8$	3,30 €	1,20 €




**In case of break-down,
send us your worn or
broken parts**

- Ask us about **different materials**
- Steels, stainless, delrin, nylon, brass, bronze, cast iron, celeron and more...
- Heat treatment on request.
Price may vary depending on the type of treatment

**CONTACT
us for a
quote**

PRODUCTIONS FROM A PLAN



• Gearing width
 • General tolerance
 • Attachment method
 - Key
 - Pin
 - Screw

GEARING CHARACTERISTICS	
Module	
Pressure angle	
Number of teeth	
Helical angle	
Pitch diameter	
Precision class	9
Centre distance	
Gear	Plan no.
Material	
Other information	



Special productions with indicative maximum sizes

		Module / Pitch	Max. sizes (mm)
STRAIGHT SPUR GEARS HELICAL GEARS		Module 0.25 to module 8 120DP to 4DP (imperial)	Ø600
INTERNAL GEARS		Module 0.25 to module 4	External Ø300
WORMS		Module 0.25 to module 4 from Ø10 x length 10mm to Ø60 x length 500mm	Length 300
WORM WHEELS		Module 0.25 to module 4	Ø350
RAILS		Module 0.25 to module 6 96DP to 6DP (imperial)	Length 3000
BEVEL GEARS		Module 0.8 to module 6	Ø300
PULLEYS	T	Pitch 2.5mm to 20mm	Ø400
	AT	Pitch 2.5mm to 20mm	
	HTD	Pitch 3mm to 8mm	
CHAIN PINIONS	SINGLE	Pitch 4mm to 19.05mm	Ø400
	DOUBLE		
	TRIPLE		

* Only given as an indication
Please contact us for more information.