

Steel cored polyurethane

Pitch T2.5

- Pitch 2.5mm
- Working temp. -30°C to +80°C
- Max. speed 40m/s
- Output up to 98%

Options



- Belt by the metre **T2.5M**
- Alternative lengths/widths

Accessories

- **AH** arm and **RE** roller belt idler

Info.

- When ordering, add the width to the part number
Eg: T2.5/120/4



Compatible with T2.5 pulley

DISCOUNTS

Qty	1+	6+	20+	40+	60+	100+
Disc.	List	-7%	-14%	-20%	-24%	On request

Part number	Length	No. of teeth	Stock*	Stock*	Price each 1 to 5 for widths		
			4mm	6mm	4mm	6mm	10mm
T 2.5/120	120,00	48	✓	✓	9,76 €	10,84 €	On request
T 2.5/145	145,00	58	✓	✓	9,89 €	10,94 €	
T 2.5/160	160,00	64	✓	✓	9,92 €	10,99 €	
T 2.5/177	177,50	71	✓	✓	10,14 €	11,26 €	
T 2.5/180	180,00	72	✓	✓	10,14 €	11,26 €	
T 2.5/182	182,50	73	✓	✓	10,14 €	11,26 €	
T 2.5/200	200,00	80	✓	✓	10,14 €	11,26 €	
T 2.5/230	230,00	92	✓	✓	10,85 €	12,09 €	
T 2.5/245	245,00	98	✓	✓	10,76 €	11,97 €	
T 2.5/265	265,00	106	✓	✓	10,86 €	12,10 €	
T 2.5/285	285,00	114	✓	✓	10,92 €	12,14 €	
T 2.5/290	290,00	116	✓	✓	11,37 €	12,67 €	
T 2.5/317	317,50	127	✓	✓	11,33 €	12,61 €	
T 2.5/330	330,00	132	✓	✓	11,46 €	12,73 €	
T 2.5/380	380,00	152	✓	✓	12,10 €	13,45 €	
T 2.5/420	420,00	168	-	✓	15,45 €	13,42 €	
T 2.5/480	480,00	192	✓	✓	12,55 €	13,92 €	
T 2.5/500	500,00	200	✓	✓	12,73 €	14,13 €	
T 2.5/600	600,00	240	✓	✓	17,43 €	19,36 €	
T 2.5/620	620,00	248	-	✓	18,09 €	20,13 €	
T 2.5/650	650,00	260	-	✓	17,71 €	19,64 €	
T 2.5/780	780,00	312	✓	✓	20,41 €	22,73 €	
T 2.5/950	950,00	380	✓	✓	22,55 €	25,09 €	

*Depending on availability - Dimensions in mm

T-type timing belts




Pitch

Steel cored polyurethane

T5

- Pitch 5mm
- Working temp. -30°C to +80°C
- Max. speed 40m/s
- Output up to 98%



Options

- Belt by the metre **T5M**
- Alternative lengths/widths

Accessories


- **AH** arm and **RE** roller belt idler

Info.

- When ordering, add the width to the part number

Eg: **T5/120/4**

Compatible with
T5 pulley



DISCOUNTS

Qty	1+	6+	20+	40+	60+	100+
Disc.	List	-7%	-14%	-20%	-24%	On request

Part number	Length	Teeth	Stock*			Price each 1 to 5 for widths				On request
			6mm	10mm	16mm	6mm	10mm	16mm	25mm	
T 5/150	150	30	✓	-	-	11,72 €	15,21 €	22,10 €		
T 5/185	185	37	✓	✓	✓	11,94 €	15,70 €	22,62 €		
T 5/200	200	40	✓	✓	✓	11,97 €	15,73 €	22,76 €		
T 5/210	210	42	-	✓	-	12,42 €	16,39 €	23,60 €		
T 5/215	215	43	-	-	-	12,07 €	15,97 €	22,98 €		
T 5/220	220	44	-	-	-	12,07 €	15,97 €	22,98 €		
T 5/225	225	45	✓	✓	✓	12,10 €	16,06 €	23,13 €		
T 5/245	245	49	✓	✓	-	12,23 €	16,29 €	23,43 €		
T 5/250	250	50	-	✓	-	12,67 €	16,80 €	24,13 €		
T 5/255	255	51	-	✓	-	12,28 €	16,29 €	23,53 €		
T 5/260	260	52	✓	-	-	12,28 €	16,29 €	23,53 €		
T 5/270	270	54	✓	✓	✓	12,33 €	16,40 €	23,62 €		
T 5/280	280	56	✓	✓	-	12,38 €	16,51 €	23,80 €		
T 5/295	295	59	-	✓	✓	12,48 €	16,73 €	24,03 €		

*Depending on availability - Dimensions in mm



Pitch T5

Qty	1+	6+	20+	40+	60+	100+
Disc.	List	-7%	-14%	-20%	-24%	On request

Part number	Length	Teeth	Stock*	Stock*	Stock*	Price each 1 to 5 for widths			
			6mm	10mm	16mm	6mm	10mm	16mm	25mm
T 5/305	305	61	✓	✓	✓	12,61 €	16,83 €	24,23 €	23 €
T 5/330	330	66	-	✓	✓	12,70 €	17,05 €	24,59 €	23 €
T 5/340	340	68	✓	✓	-	12,70 €	17,13 €	24,69 €	23 €
T 5/355	355	71	✓	✓	✓	12,83 €	17,40 €	25,02 €	23 €
T 5/365	365	73	✓	✓	✓	12,87 €	17,43 €	25,21 €	23 €
T 5/390	390	78	✓	✓	-	12,90 €	17,68 €	25,47 €	23 €
T 5/400	400	80	✓	✓	-	13,02 €	17,77 €	25,58 €	23 €
T 5/410	410	82	-	✓	✓	13,06 €	17,82 €	25,85 €	23 €
T 5/420	420	84	✓	✓	✓	13,13 €	17,90 €	25,94 €	23 €
T 5/455	455	91	✓	✓	✓	13,30 €	18,28 €	26,88 €	23 €
T 5/460	460	92	-	-	-	13,75 €	18,91 €	27,73 €	23 €
T 5/480	480	96	✓	✓	✓	13,38 €	18,69 €	27,42 €	23 €
T 5/500	500	100	✓	✓	✓	13,51 €	18,89 €	27,93 €	23 €
T 5/510	510	102	✓	-	-	13,53 €	19,05 €	28,20 €	23 €
T 5/525	525	105	-	✓	✓	13,77 €	19,34 €	28,74 €	23 €
T 5/545	545	109	-	✓	✓	14,06 €	19,57 €	29,28 €	23 €
T 5/550	550	110	✓	✓	✓	14,06 €	19,57 €	29,28 €	23 €
T 5/560	560	112	✓	✓	✓	14,13 €	19,74 €	29,52 €	23 €
T 5/575	575	115	✓	✓	✓	14,37 €	20,10 €	30,07 €	23 €
T 5/590	590	118	-	✓	-	14,85 €	20,93 €	31,57 €	23 €
T 5/610	610	122	✓	✓	✓	14,74 €	20,57 €	31,10 €	23 €
T 5/620	620	124	✓	-	-	14,83 €	20,72 €	31,41 €	23 €
T 5/630	630	126	✓	✓	-	14,97 €	20,78 €	32,00 €	23 €
T 5/650	650	130	-	-	✓	15,81 €	21,87 €	33,45 €	23 €
T 5/690	690	138	-	✓	✓	15,89 €	22,04 €	33,78 €	23 €
T 5/720	720	144	✓	-	✓	16,29 €	22,62 €	34,86 €	23 €
T 5/750	750	150	-	✓	✓	16,73 €	23,22 €	35,90 €	23 €
T 5/765	765	153	-	-	-	17,69 €	24,42 €	37,59 €	23 €
T 5/780	780	156	-	-	✓	17,27 €	23,87 €	36,75 €	23 €
T 5/815	815	163	-	✓	-	17,82 €	24,90 €	37,96 €	23 €
T 5/840	840	168	-	-	-	18,09 €	25,36 €	38,76 €	23 €
T 5/900	900	180	-	✓	-	19,05 €	26,88 €	40,65 €	23 €
T 5/990	990	198	-	-	-	20,37 €	28,91 €	43,67 €	23 €
T 5/1075	1075	215	-	-	-	21,73 €	30,09 €	47,17 €	23 €
T 5/1100	1100	220	-	-	-	22,04 €	31,34 €	47,60 €	23 €
T 5/1160	1160	232	-	-	-	23,96 €	33,69 €	51,20 €	23 €
T 5/1215	1215	243	-	✓	✓	24,44 €	33,89 €	51,97 €	23 €
T 5/1315	1315	263	-	-	-	27,77 €	37,59 €	56,85 €	23 €
T 5/1380	1380	276	-	-	✓	28,34 €	37,92 €	57,23 €	23 €

On request

*Depending on availability - Dimensions in mm

T-type belt



Pitch T10

Polyurethane with steel core

- Pitch 10mm
- Working temp. -30°C to +80°C
- Max. speed 40m/s
- Output up to 98%

Options

- Belt by the metre **T10M**
- Alternative lengths/widths

Accessories

- AH arm and RE roller belt idler

Info.

- When ordering, add the width to the part number.
Eg: **T10/120/4**



Compatible with T10 pulley


DISCOUNTS

Qty	1+	6+	20+	40+	60+	100+
Disc.	List	-7%	-14%	-20%	-24%	On request

Part number	Length	No. of teeth	Price each 1 to 5 for widths				On request	On request
			16mm	25mm	32mm	50mm		
T 10/260	260	26	27,28 €	37,85 €				
T 10/370	370	37	29,51 €	41,20 €				
T 10/410	410	41	30,57 €	42,50 €				
T 10/500	500	50	33,04 €	45,19 €				
T 10/530	530	53	33,81 €	46,33 €				
T 10/560	560	56	35,14 €	47,92 €				
T 10/600	600	60	36,14 €	49,03 €				
T 10/610	610	61	36,29 €	49,58 €				
T 10/630	630	63	37,36 €	50,64 €				
T 10/660	660	66	38,45 €	52,25 €				
T 10/680	680	68	34,35 €	57,81 €				
T 10/690	690	69	39,53 €	53,94 €				
T 10/700	700	70	41,09 €	48,90 €				
T 10/720	720	72	40,86 €	55,81 €				
T 10/730	730	73	39,16 €	61,08 €				
T 10/750	750	75	43,15 €	62,49 €				

Dimensions in mm

Pitch T10



DISCOUNTS

Qty	1+	6+	20+	40+	60+	100+
Disc.	List -7%	-14%	-20%	-24%	On request	

Part number	Length	No. of teeth	Price each 1 to 5 for widths			
			16mm	25mm	32mm	50mm
T 10/780	780	78	43,33 €	59,33 €	On request	On request
T 10/810	810	81	44,67 €	61,19 €		
T 10/840	840	84	46,06 €	63,17 €		
T 10/880	880	88	47,63 €	65,86 €		
T 10/890	890	89	48,18 €	66,96 €		
T 10/920	920	92	49,58 €	69,10 €		
T 10/960	960	96	51,18 €	72,33 €		
T 10/970	970	97	51,74 €	73,23 €		
T 10/980	980	98	52,25 €	73,97 €		
T 10/1010	1010	101	53,94 €	76,18 €		
T 10/1080	1080	108	56,90 €	81,04 €		
T 10/1110	1110	111	58,71 €	90,29 €		
T 10/1140	1140	114	59,89 €	85,44 €		
T 10/1150	1150	115	60,14 €	85,91 €		
T 10/1210	1210	121	63,17 €	90,54 €		
T 10/1240	1240	124	64,83 €	92,40 €		
T 10/1250	1250	125	65,01 €	93,27 €		
T 10/1300	1300	130	67,71 €	96,83 €		
T 10/1320	1320	132	68,57 €	98,14 €		
T 10/1350	1350	135	69,95 €	100,31 €		
T 10/1390	1390	139	72,09 €	103,34 €		
T 10/1400	1400	140	72,64 €	103,83 €		
T 10/1420	1420	142	73,47 €	105,16 €		
T 10/1460	1460	146	75,37 €	107,95 €		
T 10/1500	1500	150	On request	119,92 €		
T 10/1560	1560	156	78,63 €	114,42 €		
T 10/1610	1610	161	82,70 €	118,50 €		
T 10/1750	1750	175	90,01 €	129,90 €		
T 10/1780	1780	178	91,62 €	132,31 €		
T 10/1880	1880	188	97,05 €	140,49 €		
T 10/1960	1960	196	103,03 €	148,62 €		
T 10/2250	2250	225	127,17 €	186,73 €		

Dimensions in mm


AT-type timing belt



Pitch AT5

Steel cored polyurethane

- 2nd generation metric profile
- Transmits a greater torque
- Pitch 5mm
- Working temp. -30°C to +80°C
- Max. speed 40m/s
- Output up to 98%
- Oil-resistant
- Low noise
- Resists stretching



Info.

- When ordering, add the width to the part number.
E.g.: AT5/525/25

DISCOUNTS

Qty	1+	6+	20+	40+	60+	100+
Disc. List	-	-7%	-14%	-20%	-24%	On request

Part number	Length	No. of teeth	Price each 1 to 5 for widths		
			10mm	16mm	25mm
AT5/225	225	45	18,41 €	27,42 €	37,49 €
AT5/255	255	51	18,89 €	27,75 €	37,75 €
AT5/280	280	56	19,11 €	27,97 €	38,07 €
AT5/300	300	60	19,34 €	28,14 €	38,32 €
AT5/330	330	66	19,45 €	28,48 €	39,02 €
AT5/340	340	68	19,48 €	28,65 €	39,02 €
AT5/375	375	75	19,83 €	29,13 €	39,89 €
AT5/390	390	78	19,94 €	29,45 €	40,28 €
AT5/420	420	84	20,24 €	29,84 €	40,87 €
AT5/450	450	90	20,60 €	30,61 €	41,54 €
AT5/455	455	91	20,69 €	30,75 €	41,84 €
AT5/500	500	100	21,73 €	32,43 €	44,97 €
AT5/525	525	105	22,76 €	34,28 €	47,60 €
AT5/545	545	109	23,43 €	35,60 €	49,80 €
AT5/600	600	120	25,09 €	38,32 €	53,29 €
AT5/610	610	122	25,47 €	38,73 €	54,15 €
AT5/660	660	132	26,16 €	39,89 €	55,90 €
AT5/710	710	142	27,42 €	41,54 €	58,10 €
AT5/720	720	144	27,66 €	41,84 €	58,56 €
AT5/750	750	150	27,97 €	42,73 €	59,41 €
AT5/780	780	156	28,83 €	44,08 €	61,59 €
AT5/825	825	165	29,73 €	45,85 €	63,79 €
AT5/860	860	172	30,44 €	47,17 €	66,01 €
AT5/975	975	195	33,02 €	51,54 €	72,58 €
AT5/1050	1050	210	35,39 €	55,04 €	77,33 €
AT5/1125	1125	225	36,79 €	57,63 €	81,72 €
AT5/1500	1500	300	44,08 €	70,36 €	101,43 €
AT5/2000	2000	400	61,59 €	95,31 €	134,69 €

Dimensions en mm




AT-type timing belt

Steel cored polyurethane

Pitch AT10

- 2nd generation metric profile
- Transmits a greater torque
- Pitch 10mm
- Working temp. -30°C to +80°C
- Max. speed 40m/s
- Output up to 98%
- Oil-resistant
- Low noise
- Resists stretching



SIMPLE FACE



Din 7721

Info.

- When ordering, add the width to the part number
E.g.: AT5/525/25

DISCOUNTS

Qty	1+	6+	20+	40+	60+	100+
Disc.	List	-7%	-14%	-20%	-24%	On request

Part number	Length	No. of teeth	Price each 1 to 5 for widths		
			25mm	32mm	50mm
AT10/500	500	50	56.79 €	71.66 €	105.39 €
AT10/560	560	56	59.85 €	-	112.39 €
AT10/600	600	60	61.59 €	78.66 €	115.02 €
AT10/610	610	61	62.05 €	79.13 €	115.84 €
AT10/660	660	60	66.01 €	84.37 €	123.31 €
AT10/700	700	70	68.59 €	88.29 €	128.55 €
AT10/730	730	73	70.78 €	91.80 €	132.50 €
AT10/780	780	78	74.31 €	95.74 €	139.93 €
AT10/800	800	80	76.47 €	97.49 €	141.70 €
AT10/840	840	84	79.99 €	102.30 €	149.13 €
AT10/890	890	89	85.69 €	110.16 €	160.53 €
AT10/920	920	92	89.17 €	115.44 €	168.41 €
AT10/960	960	96	94.88 €	123.31 €	178.03 €
AT10/980	980	98	97.90 €	124.63 €	187.21 €
AT10/1000	1000	100	100.10 €	128.13 €	190.28 €
AT10/1010	1010	101	100.97 €	128.55 €	191.56 €
AT10/1050	1050	105	102.75 €	132.09 €	195.53 €
AT10/1080	1080	108	104.05 €	133.80 €	197.29 €
AT10/1100	1100	110	106.25 €	136.00 €	201.21 €
AT10/1150	1150	115	108.86 €	139.93 €	207.31 €
AT10/1200	1200	120	111.48 €	143.84 €	212.60 €
AT10/1210	1210	121	111.94 €	144.74 €	213.89 €
AT10/1250	1250	125	115.02 €	147.82 €	218.30 €
AT10/1280	1280	128	115.84 €	150.02 €	220.89 €
AT10/1300	1300	130	117.62 €	151.75 €	223.52 €
AT10/1320	1320	132	119.37 €	153.95 €	227.45 €
AT10/1350	1350	135	122.00 €	156.99 €	232.71 €
AT10/1360	1360	136	123.31 €	158.33 €	234.92 €
AT10/1400	1400	140	126.80 €	164.45 €	242.37 €
AT10/1480	1480	148	133.80 €	174.04 €	256.80 €
AT10/1500	1500	150	135.13 €	176.28 €	259.85 €
AT10/1600	1600	160	143.84 €	188.05 €	277.38 €
AT10/1700	1700	170	153.07 €	199.46 €	295.30 €
AT10/1720	1720	172	155.25 €	201.21 €	298.35 €
AT10/1800	1800	180	161.82 €	211.26 €	312.37 €
AT10/1860	1860	186	167.09 €	217.84 €	321.55 €
AT10/1940	1940	194	174.96 €	229.67 €	339.97 €

Dimensions in mm